

# FD3-PA096J00U4210



FDH 3000 Fiber Distribution Hub in a Pedestal, 96F, SC/APC, no splitters, stranded pigtails, 96 splice cap, 4 splice trays, 6FF

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

## Product Classification

|                              |                   |
|------------------------------|-------------------|
| <b>Regional Availability</b> | North America     |
| <b>Product Type</b>          | Hub in a pedestal |
| <b>Product Series</b>        | FDH 3000          |

## General Specifications

|  |                     |
|--|---------------------|
| <b>Access</b>                            | Front   Rear        |
| <b>Cable Type</b>                        | Pigtails - Stranded |
| <b>Color</b>                             | Green               |
| <b>Distribution Ports, quantity</b>      | 96                  |
| <b>Fibers per Feeder Cable, quantity</b> | 6                   |
| <b>Interface, Input</b>                  | SC                  |
| <b>Interface Feature, Input</b>          | APC                 |
| <b>Mounting</b>                          | Pedestal            |
| <b>Splice Tray Included, quantity</b>    | 4                   |
| <b>Splice Tray Type Included</b>         | 24-way, heat shrink |
| <b>Splicing Capacity, maximum</b>        | 96                  |
| <b>Splitter Slots, quantity</b>          | 6                   |

## Dimensions

|                       |                    |
|-----------------------|--------------------|
| <b>Height</b>         | 889 mm   35 in     |
| <b>Width</b>          | 292.1 mm   11.5 in |
| <b>Depth</b>          | 368.3 mm   14.5 in |
| <b>Enclosure Size</b> | Small              |

# FD3-PA096J00U4210

---

## Material Specifications

**Material Type** Molded plastic

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Included** Cable clamps (2)

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

| Agency     | Classification  |
|------------|---|
| CHINA-ROHS | Above maximum concentration value   |
| REACH-SVHC | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant/Exempted  |
| UK-ROHS    | Compliant/Exempted  |

