



ERA® Wireless Communications Switch Subrack, 2 U

Product Classification

| | |
|----------------------|---------|
| Product Type | Subrack |
| Product Brand | ERA® |

General Specifications

| | |
|----------------------------------|---|
| Mounting | Rack |
| Note | Detailed Product Specifications are available. Please contact your local ANDREW representative. |
| Rack Type | EIA 19 in |
| Slots Available, quantity | 11 |

Dimensions

| | |
|---------------|--------------------|
| Height | 88.5 mm 3.484 in |
| Width | 482 mm 18.976 in |
| Depth | 450 mm 17.717 in |

Packaging and Weights

| | |
|-----------------------|-----------------------|
| Height, packed | 540 mm 21.26 in |
| Width, packed | 600 mm 23.622 in |
| Depth, packed | 200 mm 7.874 in |
| Included | Fan filter Fan tray |
| Weight, gross | 10 kg 22.046 lb |
| Weight, net | 7.96 kg 17.549 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS | Compliant/Exempted |

UK-ROHS

Compliant/Exempted

