FD5M-288S00DDB4P



Small FDH cabinet with 288 ports, LC/APC, no splitters, dry dielectric flat ribbon, 100 ft stub, 72F feeder, 288F distribution pole/wall mount

Product Classification

Regional Availability Latin America | North America

Product Type Fiber distribution hub

Product Series FDH 5000

General Specifications

Access Front

Cable TypePigtails - Ribbon

Color Putty white

Distribution Cables, quantity 1

Distribution Ports, quantity 288

Fibers per Distribution Cable, quantity 288

Fibers per Feeder Cable, quantity 72

Mounting Wall/Pole Mount, mounting kit included

Splitter Slots, quantity 9

Dimensions

Height 609.6 mm | 24 in

Width 336.55 mm | 13.25 in

Depth 190.5 mm | 7.5 in

Cable Length 30.48 m | 100 ft

Enclosure Size Small

Material Specifications

Finish Powder coated

Material Type Aluminum



FD5M-288S00DDB4P

Environmental Specifications

Environmental Space Above ground | Aerial

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

