FD5M-864S00DEB5P



FDH5000 cabinet with 864 ports, LC/APC, no splitters, dry dielectric flat ribbon, 100 ft stub, 144F feeder, 2x 432F distribution, pole mount

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution hub
Product Series	FDH 5000
General Specifications	
Access	Front
Cable Type	Pigtails - Ribbon
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	864
Fibers per Distribution Cable, quantity	288
Fibers per Feeder Cable, quantity	144
Mounting	Pole
Splitter Slots, quantity	9
Dimensions	
Height	698.5 mm 27.5 in
Width	698.5 mm 27.5 in
Depth	228.6 mm 9 in
Cable Length	30.48 m 100 ft
Enclosure Size	Large
Material Specifications	
Finish	Powder coated

Material Type

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 29, 2024

Steel



FD5M-864S00DEB5P

Environmental Specifications

Environmental Space

Above ground | Aerial

Packaging and Weights

Packaging quantity

Packaging Type

Pallet

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 29, 2024

