

M4800-PANELS

Base Product



SYSTIMAX M4800 Series Modular Panels, 48 ports, for Cat 5E, 6, and 6A Jacks

Product Classification

Portfolio	CommScope®
Product Type	RJ45 patch panel

General Specifications

Rack Type	EIA 19 in
Rack Units	1

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL