

WB-K0710-B



Safety Grated Waveguide Bridge Kit, 7 in x 10 ft, with two 13 ft 4 in direct burial posts

Product Classification

Portfolio	CommScope®
Product Type	Waveguide bridge kit
Ordering Note	CommScope® non-standard product
Warranty	One year

General Specifications

Application	Direct burial
Cable Runs, quantity	12
Pipe, quantity	2
Height	4064 mm 160 in
Width	177.8 mm 7 in
Length	3048 mm 120 in
Pipe Length	4,053.84 mm 159.6 in

Dimensions

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Packaging and Weights

Included	Caps Channel Hardware Posts Support brackets Trapeze
Packaging quantity	1
Weight, net	137 kg 302.033 lb

Included Products

- MF-130 – Direct Burial Pipe Column, 13 ft 4 in
- WB-CY110 – Safety Grated Waveguide Bridge Channel, 12 in x 10 ft

WB-K0710-B

- WB-LB12-3 – Waveguide Bridge Support Bracket, 12 in wide for 3-1/2 in OD legs
- WB-T12-3 – Trapeze Kit, triple tee, 12 in wide, three rungs

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines