

F1A-PNMNM-15M



FSJ1-50A SureFlex® Jumper with interface types N Male and N Male, 15 m

Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	15 m 49.213 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	15

Jumper Assembly Sample Label

F1A-PNMNM-15M



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

FSJ1-50A

- FSJ1-50A, HELIAX[®] Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket