

4


3

2

1

- 1.0 GENERAL NOTES
 - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X.X]
 - 1.2 FEATURES CRITICAL TO QUALITY ARE INDICATED IN ROUNDED BOX (XX)
 - 1.3 3D DIGITAL FILES ARE FOR REFERENCE. IN CASE OF CONFLICT FOLLOW PDF DRAWING
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 - 3.1 BREAK SHARP EDGES AND DEBURR PART FOR SAFE HANDLING
 - 3.2 GALVANIZE PER ASTM A123
 - 3.3 MARK WITH PART NUMBER, REVISION, AND VENDOR ID WITH ETCH, STAMP OR LABEL. CHARACTERS TO BE 0.12" TO 0.24" HIGH AND LEGIBLE TO THE UNAIDED EYE.
- 4.0 TEST
- 5.0 PACKAGING
 - 5.1 PACKAGING SHALL MEET COMMScope REQUIREMENTS PER DOCUMENT IS-PL-3005

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	LL1090 26SEP23	YZ1080 40179492CMO
B	UPDATED NOTES AND REMOVED BARE LEVEL	LL1090 28AUG24	BA1025 40203400CMO



COMMScope, INC. OF NORTH CAROLINA												
TOLERANCES						SAP MATERIAL MASTER						
1 PLACE .X[X] ± 0.2[6.3]			3 PLACE .XXX[X] ± 0.060[1.5]			74916-2-001-114						
2 PLACE .XX[X] ± 0.12[3.0]			ANGLES ± 2°									
FINISH GALV A123						MATERIAL A500						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	CE	LL1090	26SEP23	MOSAIC-MOUNT, 2-7/8" X 114"								
	RW	YMENG	08/28/2024									
	AD	BA1025	08/28/2024									
	RE	YMENG	08/28/2024									
	ECN	40203400CMO										
SCALE		DOCUMENT NO.										
1:2		74916-2-001-114										
SIZE	Auth Group	INSL	MODEL			DRAWING			SHEET			
C			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	01	RE	B	1 OF 1

DENSITY	60.70	lbs/in ³
MASS	60.70	lbs
VOLUME	213.48	in ³
SURFACE AREA	2118.01	in ²
HEIGHT	2.875"	
LENGTH	114.00"	
WIDTH	11.38"	

4

3

2

1