

# 3-1920743-0

---



Fiber Optic Patch Cord, Duplex, Multimode, LC/UPC to LC/UPC, 30 m

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   China   India |
| <b>Portfolio</b>             | CommScope®                                   |
| <b>Product Type</b>          | Fiber patch cord, duplex                     |
| <b>Product Series</b>        | 192  |

## General Specifications

|                               |        |
|-------------------------------|--------|
| <b>Connector A, quantity</b>  | 2      |
| <b>Color, boot A</b>          | Beige  |
| <b>Color, connector A</b>     | Beige  |
| <b>Connector B, quantity</b>  | 2      |
| <b>Color, boot B</b>          | Beige  |
| <b>Color, connector B</b>     | Beige  |
| <b>Interface, Connector A</b> | LC/UPC |
| <b>Interface, Connector B</b> | LC/UPC |
| <b>Jacket Color</b>           | Aqua   |
| <b>Total Fibers, quantity</b> | 2      |

## Dimensions

|                             |                   |
|-----------------------------|-------------------|
| <b>Cord Length</b>          | 30 m   98.425 ft  |
| <b>Diameter Over Jacket</b> | 1.8 mm   0.071 in |

## Ordering Tree

# 3-1920743-0

---



## Optical Specifications

**Fiber Mode** Multimode  
**Fiber Type** OM3, LazrSPEED®

## Environmental Specifications

**Environmental Space** Low Smoke Zero Halogen (LSZH)

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

