




NOTES:

| REVISIONS | | | |
|-----------|-------------|------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | | | |



RVVS4-65S-R3

| | | | | | | | | | | |
|--|------------|---------------|-----------|----------------|---------------------|--------|----------|--------|--|--|
| COMMSCOPE, INC. OF NORTH CAROLINA | | | | | | | | | | |
| TOLERANCES | | | | | SAP MATERIAL MASTER | | | | | |
| 0 PLACE X ± | | 2 PLACE .XX ± | | | | | | | | |
| 1 PLACE .X ± | | ANGLES ± | | | | | | | | |
| FINISH | | | | | MATERIAL | | | | | |
| PRODUCT DRAWING | | | | | | | | | | |
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002) | | NAME | DATE | TITLE | | | | | | |
| | | CE WY1013 | 4/26/2022 | RVVS4-65S-R3-L | | | | | | |
| | | RW | | | | | | | | |
| | | AD | | | | | | | | |
| | | RE | | | | | | | | |
| ECN | | | SCALE | DOCUMENT NO. | | | | | | |
| | | | 1:4 | RVVS4-65S-R3-L | | | | | | |
| SIZE | Auth Group | MODEL | | DRAWING | | | SHEET | | | |
| A2 | | VERSION | STATUS | REVISION | VERSION | STATUS | REVISION | 1 OF 1 | | |

| | |
|--------------|-------------------|
| DENSITY | g/mm ³ |
| MASS | grams |
| VOLUME | mm ³ |
| SURFACE AREA | mm ² |
| HEIGHT | |
| LENGTH | |
| WIDTH | |