NG4-APMP0400EB



NG4access® Adapter Pack Universal Kit, 4 MPO Adapters, enhanced Method B (key up/up)

- Adapter ports are staggered for easy connector insertion/removal, and help to clearly identify individual adapter ports
- Each chassis can be loaded with up to 48 adapter packs while two adapter packs snap into a single access tray

Product Classification

Regional Availability Latin America | North America

Product Type Fiber adapter pack

Product Brand NG4access®

Product Series NG4

General Specifications

Application For use with NG4 panels

Adapters, quantity, front 4

Body Style Simplex | Straight orientation

Color, front Putty white

Interface MPO

Total Ports, quantity, front 48

Optical Specifications

Fiber Mode | Multimode | Singlemode

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+40 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +104 $^{\circ}\text{F}$)

Storage Temperature $-5 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications



NG4-APMP0400EB

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

