

TES-SS-MSK14 | UNIVERSAL ADJUSTABLE CROSSOVER



Universal Crossover Plate,Round - joins range of 2-3/8 up to to 3-1/2 in OD round members

Product Classification

Product Type Clamp plate

General Specifications

Mounting Crossover plate

Dimensions

Height	139.7 mm 5.5 in
Width	139.7 mm 5.5 in
Length	266.7 mm 10.5 in
Mounting Diameter 2, maximum	88.9 mm 3.5 in
Mounting Diameter 2, minimum	60.96 mm 2.4 in
Mounting Diameter, maximum	88.9 mm 3.5 in
Mounting Diameter, minimum	60.96 mm 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included	Hardware Plates
Packaging quantity	1
Weight, net	5 kg 11.023 lb