NG4-WDM-MODULES

Base Product



NG4access xWDM Module

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

CWDM & DWDM VAMs Coarse Wavelength Division Mulitiplexing (CWDM) and Dense Wavelength Division Mulitiplexing (DWDM) VAMs are used to combine (or separate) two or more signals with different wavelengths.

CWDM VAM modules provide a wide range of wavelength combinations from 4 to 8 channels while DWDM VAM modules are typically used for higher channel count requirements and combine 8 to 40 channels based on the ITU DWDM wavelengths.

Both CWDM and DWDM modules are available with up to 12 SC or 24 LC front facing connectors. Test ports are available for signal turn-up and test access.

NG4access CWDM VAMs occupy one access tray in the universal chassis. NG4access DWDM VAMs occupy either one, two or three access trays in the universal chassis. The NG4access universal chassis holds up to 12 left and 12 right orientation single high VAMs. Which easily snap into place.

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type CWDM module | DWDM module

Product Brand NG4access®
Product Series FACT | NG4

Government FundingBuild America Buy America (BABA) compliant*

Warranty For more information, please consult our Product Warranty guidelines

General Specifications

Device Type Plug-and-play module

Functionality Demultiplexing | Multiplexing

Application For use with NG4 access frames

Interface, frontLC/APC| LC/UPCInterface, InputLC/APC| LC/UPCInterface, OutputLC/APC| LC/UPC

COMMSCOPE®

NG4-WDM-MODULES

Tray Orientation Left orientation | Right orientation

Dimensions

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 130.3 mm | 5.13 in

Packaging and Weights

Packaging quantity 1

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

