

SRC3-U5A1B1BL003-US



NOVUX™ Specialty Range Closure 100, splice only, no adapter, no splitter, 12 splices, SMOUV® 45mm & 12-way ribbon splice protectors, black, 2x NVX-CR-MC-FT-NN cable retention, 2x pre-installed FHD-F01K-0003M, Build America Buy America (BABA)

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information
- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

| | |
|-----------------------------------|---|
| Regional Availability | Asia EMEA Latin America North America |
| Regional Availability Note | Contact your local CommScope representative for specific availability |
| Product Type | Single-ended, rectangular fiber closure |
| Product Brand | NOVUX™ |
| Product Series | SRC100 |
| Government Funding | Build America Buy America (BABA) coming soon* |

General Specifications

| | |
|--|---|
| Cable Capacity, Drop | 4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 4 Round 1.2–8.0 mm (0.05–0.31 in) |
| Cable Ports Quantity, total | 4 multi-out ports (8 cables) |
| Cable Sealing Type | Compressed gel |
| Cable Termination Attachments, quantity | 2 |
| Closure Sealing Type | Hinged with latch |
| Closure Style | Single-ended |
| Color | Black |
| Mounting | Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included |
| Network Area Type | Drop |

SRC3-U5A1B1BL003-US


| | |
|--|-------------------------|
| Port Type | No adapter No adapter |
| Port, quantity | 0 |
| Splice Tray Included, quantity | 1 |
| Splice Tray Type Included | 12-way, heat shrink |
| Splicing Capacity, maximum | 12 |
| Splicing Capacity, Single Fusion, maximum | 12 |
| Splicing Type, Supported | Single fusion |
| Splitter Type | No splitter |
| Splitter, quantity | 0 |

Dimensions






| | |
|---------------------------------------|--------------------|
| Height | 267 mm 10.512 in |
| Width | 117 mm 4.606 in |
| Depth | 49 mm 1.929 in |
| Cable Entry Drop Port Diameter | 8 mm (0.31 in) mm |

Ordering Tree

SRC3-U5A1B1BL003-US



2 cable attachments are supplied.

| Cable retention* | Cable Termination Unit (CTU) options | | | | |
|---|--|--|--|--|--|
| A None | B  | C  | D  | E  | F  |
| B NVX-CR-MC-FT-NN | NVX-CR-MC-FT-NN | NVX-CR-MC-RD-NN | NVX-CR-SA-SM-NN | NVX-CR-TI-SM-NN | NVX-CR-DU-FL-NN |
| C NVX-CR-MC-RD-NN | • Flat cable | • Round cable | • Round cable | • Round cable | • Round cable |
| D NVX-CR-SA-SM-NN | • Metal clip | • Metal clip | • Dia up to 8 mm | • Dia up to 8 mm | • Dia up to 6.2 mm |
| E NVX-CR-TI-SM-NN | • Range 3 x 5 to 4 x 8 mm | • Range 4 to 6.2 mm | • Strength member | • Aramide yarns | • Aramide yarns |
| F NVX-CR-DU-FL-NN | | | • Aramide yarns | • Single layer | • Dual layer |
| G 4xNVX-CR-MC-FT-NN | | | • Single layer | | • Compact length |
| H 4xNVX-CR-MC-RD-NN | | | | | |
| I 4xNVX-CR-SA-SM-NN | | | | | |
| J 4xNVX-CR-TI-SM-NN | | | | | |
| K 4xNVX-CR-DU-FL-NN | | | | | |
| L 2xNVX-CR-MC-FT-NN and 2xNVX-CR-MC-RD-NN | | | | | |

Material Specifications

Material Type Impact-resistant polymer

Optical Specifications

Fiber Type G.652.D | G.657.A1 | G.657.A2 | G.657.B3

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Above ground | Below ground | Direct burial

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

SRC3-U5A1B1BL003-US

Water Resistance

Flash test valve at 2 psi (20 kPa)

Packaging and Weights

Packaging quantity

10

Packaging Type

Box | Carton

Included Products

- NVX-CR-MC-FT-NN – NOVUX™ Cable Termination Unit (CTU) for flat cables with 3x5 to 4x8 mm diameter, metal clip