

# RT-DF15-B

---

PIM-Guard High Capacity DUAL Non-Penetrating Roof Frame with Optimized Antenna Spacing 15 ft face, Base Frame Only



## Product Classification

**Product Type** Non-penetrating roof frame

## General Specifications

**Mounting** Non-penetrating

**Pipe, quantity** 0

## Dimensions

**Height** 2,252.98 mm | 88.7 in

**Face Width** 4.572 m | 15 ft

**Width** 4,572 mm | 180 in

**Length** 2.377 m | 7.8 ft

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Ballast tray | Frame

**Packaging quantity** 1

## \* Footnotes

# RT-DF15-B

---

**Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code