

RT-NF11-B



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 11 ft face, Base Frame Only

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Pipe, quantity 0

Dimensions

Height 2,252.98 mm | 88.7 in

Face Width 3.353 m | 11 ft

Width 3,352.8 mm | 132 in

Length 2.377 m | 7.8 ft

Face Support Pipe Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ballast tray | Frame

Packaging quantity 1

Weight, net 383.6 kg | 845.692 lb

RT-NF11-B

* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code