

# RT-NF13-4-120

---



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 13 ft face, four 2-7/8 in OD x 120 in pipes

## Product Classification

**Product Type** Non-penetrating roof frame

## General Specifications

**Mounting** Non-penetrating

**Pipe, quantity** 4

## Dimensions

**Height** 3,048 mm | 120 in

**Face Width** 3.962 m | 13 ft

**Width** 3,962.4 mm | 156 in

**Length** 2.377 m | 7.8 ft

**Pipe Length** 3,048 mm | 120 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Ballast tray | Frame | Plain end pipes (4)

**Packaging quantity** 1

# RT-NF13-4-120

---

**Weight, net** 537.4 kg | 1,184.763 lb

\* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code