

760253291 | EPX-2U-MOD-ENC-FX-W

EPX 2U fixed panel, accepts (8) G2 style splice cassettes, modules or adapter packs, providing up to 96 duplex LC ports, white

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel Fiber patch/splice panel
Product Series	EPX

General Specifications

Application	Accepts eight G2 modular cassettes
Color	White
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	8
Rack Type	EIA 19 in
Rack Units	2
Shelf Movement	Fixed
Total Fibers, quantity	192
Total Ports, quantity	0

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	412.75 mm 16.25 in

Environmental Specifications

Safety Standard	CSA 22.2 UL 1863
------------------------	--------------------

Packaging and Weights

Packaging quantity	1
Weight, net	3.62 kg 7.98 lb