

# 760253292 | EPX-4U-MOD-ENC-W

---

EPX 4U sliding panel, accepts (16) G2 style splice cassettes, modules or adapter packs, providing up to 192 duplex LC ports, white

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber patch panel   Fiber patch/splice panel                        |
| <b>Product Series</b>        | EPX   |

## General Specifications

|  |                                      |
|--|--------------------------------------|
| <b>Application</b>                         | Accepts sixteen G2 modular cassettes |
| <b>Color</b>                               | White                                |
| <b>Intelligence Type</b>                   | Not iPatch® ready                    |
| <b>Interface, front</b>                    | Unloaded                             |
| <b>Module/Adapter Pack Slots, quantity</b> | 16                                   |
| <b>Rack Type</b>                           | EIA 19 in                            |
| <b>Rack Units</b>                          | 4                                    |
| <b>Shelf Movement</b>                      | Sliding                              |
| <b>Total Fibers, quantity</b>              | 384                                  |
| <b>Total Ports, quantity</b>               | 0                                    |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 177.8 mm   7 in      |
| <b>Width</b>  | 482.6 mm   19 in     |
| <b>Depth</b>  | 412.75 mm   16.25 in |

## Environmental Specifications

|                        |                    |
|------------------------|--------------------|
| <b>Safety Standard</b> | CSA 22.2   UL 1863 |
|------------------------|--------------------|

## Packaging and Weights

|                           |                    |
|---------------------------|--------------------|
| <b>Packaging quantity</b> | 1                  |
| <b>Weight, net</b>        | 7.439 kg   16.4 lb |