



▶ NNV4S4-360S-F2



VIEW A-A  
BRACKET NOT SHOWN

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 40171566CMO: REL TO PRODUCTION PER EAO 612208.	15JUNE23 PHS	KVK/RD
B	ECR40188144CMO: MODEL UPDATED WITH SMALL I/P CABLE CONNECTOR .	02FEB24 PN	KVR/RD



<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>														
TOLERANCES						SAP MATERIAL MASTER								
0 PLACE X ±			2 PLACE .XX ±			1 PLACE .X ±			ANGLES ±					
FINISH						MATERIAL								
<b>PRODUCT DRAWING</b>														
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002)		NAME		DATE		TITLE								
		CE SPHARAKATE		06/15/2023		<b>NNV4S4-360S-F2-L</b>								
		RW NPHATAK		02/02/2024										
		AD KK1100		02/02/2024										
		RE DL1048		02/02/2024										
ECN 40188144CMO						SCALE <b>1:3</b>		DOCUMENT NO.						
SIZE <b>A2</b>		WORK AREA		BSA		MODEL		DRAWING				SHEET		
LENGTH		WIDTH		VERSION		STATUS		REVISION		VERSION		STATUS		REVISION
				01		RE		B		01		RE		B

DENSITY	g/mm <sup>3</sup>
MASS	grams
VOLUME	mm <sup>3</sup>
SURFACE AREA	mm <sup>2</sup>
HEIGHT	
LENGTH	
WIDTH	