



PATCHMAX® BP2100 Blank Plate

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Blank plate
<b>Product Brand</b>	PATCHMAX®

## General Specifications

<b>ANSI/TIA Category</b>	5e
<b>Color</b>	Black

## Material Specifications

<b>Material Type</b>	Powder-coated steel
----------------------	---------------------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

