



## OFDC-A4 Fiber Optic Splice/Patch Closure, gel cable sealing, 24 splices, 4 LC/APC duplex adapters, 8 pigtails (8 colors)

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for micro-sheet cables only
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

### Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Series</b>	OFDC


### General Specifications

<b>Cable Ports Quantity, total</b>	2 round ports + 4 multi-out ports (8 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Manhole   Pedestal   Strand   Wall
<b>Port Type</b>	LC/APC
<b>Splice Tray Included, quantity</b>	1
<b>Splice Tray Type Included</b>	24-way, heat shrink
<b>Splitter Type</b>	No splitter
<b>Splitter, quantity</b>	0

### Dimensions

<b>Height</b>	70 mm   2.756 in
<b>Width</b>	94 mm   3.701 in
<b>Length</b>	211 mm   8.307 in

## Ordering Tree



## Material Specifications

**Material Type** Rugged polymer

## Environmental Specifications

**Installation temperature** -5 °C to +45 °C (+23 °F to +113 °F)  
**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)  
**Relative Humidity** 93%, non-condensing  
**Environmental Space** Above ground | Below ground  
**Qualification Standards** IEC 60529, IP68 + 2 m waterhead  
**UV Resistance** UV stabilized

## Packaging and Weights

**Packaging quantity** 1  
**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

