SSC-760237600XXX | Radio Enclosure Micro for Sam, Nokia, Erc Radios

Middle of Pole Micro Concealment Enclosure for up Low, Mid, and High Power Samsung, Ericsson, and Nokia Radios

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760237600E1x Ericsson
SSC-760237600S1x Samsung
SSC-760237600N1x Nokia
SSC-760237600N3x Nokia

Includes Standard Mounting kit for through bolt, clamp, and banding

Product Classification

Portfolio	CommScope®
Product Type	Mid pole
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Notes	SSC-760237600xx1 - Light Grey | SSC-760237600xx2 - Green | SSC-760237600xx3 - Black | SSC-760237600xx4 - Brown
Color Options	Beige-Grey (RAL 7006) | Black | Black Green (RAL 6012) | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White | Umbra Grey (RAL 7022)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles | Tapered poles | Wood poles
Power Supply Compatibility	CCI PSU-1200W-48-N | DELTA 1.0 | DELTA 2.0 | PSU-AC-08
Radio Compatibility, Ericsson	220x | 440x | 4415 | 4426 | 4449 | 4478 | 8843 | Diplexer | PSU-AC-08 | Power Distribution
Radio Compatibility, Nokia	AHBCA | AHFIA | AHFIB | AHFIC | AHLBA | CCI | Diplexer | Power Distribution
Radio Compatibility Samsung	Diplexer | Power Distribution | RFV01U-D1A | RT2201-46A | RT4401-48A
Radios Included	None

Dimensions

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 30, 2021

SSC-760237600XXX | Radio Enclosure Micro for Sam, Nokia, Erc Radios

Height	1,117.6 mm | 44 in
Width	533.4 mm | 21 in
Depth	508 mm | 20 in

Electrical Specifications

Power/Fiber Input	Trade size knockouts at rear side

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum | Steel

Environmental Specifications

Thermal Compliance	GR-487

Packaging and Weights

Volume	0.303 m^3 | 10.7 ft^3
Weight (loaded)	136.078 kg | 300 lb
Weight (unloaded)	49.895 kg | 110 lb

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 30, 2021