SF-HPM3-96

Heavy Duty Square T-Arm Base Kit with two 8 ft, 2–7/8 in OD face pipe supports, includes pipe

Product Classification

Product Type	Co-location dual pipe mount kit

General Specifications

Mounting	Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD
Pipe, quantity	2
Tower Taper	Non-tapered | Tapered

Dimensions

Height	2,438.4 mm | 96 in
Face Width	1.676 m | 5.5 ft
Width	1,676.4 mm | 66 in
Length	609.6 mm | 24 in
Pipe Length	2,438.4 mm | 96 in
Mounting Diameter, maximum	203.2 mm | 8 in
Mounting Diameter, minimum	0 mm | 0 in
Pipe Outer Diameter	73.66 mm | 2.9 in
Stand-off Distance	508 mm | 20 in

Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	120 mph (BWS) at 100 ft AGL
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 30, 2024

SF-HPM3-96

Included	Clamps | Frame | Pipe mounts | Pipes | Saddle mounts
Packaging quantity	1
Weight, net	125.191 kg | 276 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 30, 2024