UDXLULU62

Base Product



Ultra Low Loss OM4, LC/UPC Uniboot to LC/UPC Uniboot, 2.0 mm Duplex Fiber Patch Cord, Plenum

- Patch cords using Uniboot technology combine, modularity, flexibility with easy insertion and removal from connectivity
- Uniboot connectors feature an adjustable polarity via a manual and independent rotation of each single connector body without exposing the fibers
- Uniboot technology features a push-pull mechanism operated by squeezing the connector boot

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Brand SYSTIMAX ULL

Product Series UDX

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, connector A Beige Color, connector B Beige Interface, Connector A LC/UPC Interface Feature, connector A Uniboot Interface, Connector B LC/UPC Interface Feature, connector B Uniboot **Jacket Color** Aqua **Total Fibers, quantity** 2

Dimensions

Cable Assembly Length Range (m) 1 - 999


Cable Assembly Length Range (ft) 1 - 999

Diameter Over Jacket 2 mm | 0.079 in

COMMSCOPE®

UDXLULU62

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Insertion Loss, maximum0.15 dBReturn Loss, minimum35 dB

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Plenum

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSAbove maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemROHSCompliant/ExemptedUK-ROHSCompliant/Exempted



Included Products

760251110 – Fiber indoor cable, LazrSPEED® Plenum Light Duty Interconnect Cordage, 2 fiber, Multimode P-002-MP-5K-F20AQ/LTS OM4, Feet jacket marking, Aqua jacket color

Page 2 of 3

UDXLULU62

860658161

- 2.0 mm LC/UPC Uniboot GEN 1.5, Aqua

