

# 760089417 | VCM-DS-96-12B

Vertical Cable Management Kit, 12in X 96in (305mm X 2438mm) Double Sided, With Doors, Black

## OBSOLETE

This product was discontinued on: January 31, 2020

### Replaced By:

760244806  
VCM-DS-96-12B

Vertical Cable Management Kit, 12in X 96in (305mm X 2438mm) Double Sided, With Doors, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Vertical cable management

## General Specifications

<b>Configuration Type</b>	Double-sided
<b>Color</b>	Black
<b>Door, quantity</b>	2

## Dimensions

<b>Height</b>	2,438.4 mm   96 in
<b>Width</b>	304.8 mm   12 in
<b>Depth</b>	558.8 mm   22 in

## Material Specifications

<b>Finish</b>	Powder-coated, smooth
<b>Material Type</b>	Aluminum

## Environmental Specifications

<b>Safety Standard</b>	UL   cUL
------------------------	----------

## Packaging and Weights

<b>Included</b>	Four 1/2-20 hex nuts   Four 1/2-20 x 1 in hex head bolts   Four flat washers   Instruction sheet   Two spools
-----------------	---

**Packaging quantity** 1  
**Packaging Type** Assembled

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Included Products

760073007 – Cable Management Spool, 2 Spools  
CABLE-MGT-SP

# 760073007 | CABLE-MGT-SP



Cable Management Spool, 2 Spools

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Cable management hardware

## General Specifications

<b>Color</b>	Black
--------------	-------

## Material Specifications

<b>Material Type</b>	Plastic
----------------------	---------

## Environmental Specifications

<b>Safety Standard</b>	UL   cUL
------------------------	----------

## Packaging and Weights

<b>Packaging quantity</b>	2
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

