204673-24

Packaging quantity

Weight, gross



24 Port Entrance Panel, 4 x 6

Product Classification	
Product Type	Entrance panel
Ordering Note	CommScope® non-standard product
General Specifications	
Color	Gray
Entry Panel Port Size	101.6 mm 4 in
Number of Ports	24
Panel Type	Multiple
Dimensions	
Height	787.4 mm 31 in
Width	1,003.3 mm 39.5 in
Material Specifications	
Material Type	Aluminum
Environmental Specification	วทร
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66
Packaging and Weights	
Height, packed	668.02 mm 26.3 in
Width, packed	459.74 mm 18.1 in
Length, packed	50.8 mm 2 in
Included	Entry cap Hardware Port

1

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 13, 2024

2.5 kg | 5.512 lb

COMMSCOPE®

204673-24

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Included Products

CAP-4 – Snap-in Entry Port Cap, 4 in

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 13, 2024



CAP-4



Snap-in Entry Port Cap, 4 in

Product Classification

Product Type	Port cap
Ordering Note	CommScope® non-standard product

General Specifications

Color	Black
Entry Panel Port Size	101.6 mm 4 in
Panel Type	Multiple

Material Specifications

Packaging and Weights

Height, packed	127 mm 5 in
Width, packed	127 mm 5 in
Length, packed	248.92 mm 9.8 in
Included	Entry cap
Packaging quantity	1
Weight, gross	0.02 kg 0.044 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 13, 2024



Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 13, 2024

COMMSCOPE®