



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 96 E2000/APC, singlemode, right oriented, putty white

Product Classification

Product Series	NGF
Product Type	Fiber patch/splice block
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Depth	495.30 mm 19.50 in
Height	558.80 mm 22.00 in
Width	166.88 mm 6.57 in

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Qualification Standards	Telcordia GR-449-CORE
Relative Humidity	Up to 80%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Shelf Movement	Fixed
Application	Used in NGF-style frames only
Body Style	Right orientation
Color	Putty white
Color, front	Putty white
Door Type, front	Compression latch Hinged
Functionality	Patching Splicing

Growth Configuration	Fully loaded
Includes	Mounting hardware
Interface Feature, front	APC
Interface, front	E2000
Package Quantity	1
Rack Type	NGF
Total Ports, quantity	96

Mechanical Specifications

Cable Exit Location	Rear, bottom side
----------------------------	-------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

