



FIST™ Splice Sub-assembly kit with 2 trays, each for holding up to 1 12-strip ribbon fiber, with Heat Shrink type splice holder

- Splice sub-assemblies consists of a wraparound groove plate holding the included splice organizer trays
- Groove plates are designed with slots for routing fiber to and from the organizer trays
- Loop-back facility allowing for single circuit uncut looped fiber storage on the splice tray
- Compliant with most splice types and independent of any optical fiber construction

Product Classification

Product Type	Fiber splice tray
Product Series	FIST-SOSA2
Regional Availability	EMEA
Product Brand	FIST™


General Specifications

Application	For use with BUDI fiber wall boxes For use with FIST fiber splice closures For use with FIST fiber splice panels
Color	Gray
Fiber Storage Length, maximum	2050 mm for 12-ribbon fibers
Fiber Storage Length, minimum	650.00 mm 25.59 in
Package, quantity	1
Packaging Type	Bag Carton
Splice Protector Diameter, maximum	5.00 mm 0.20 in
Splice Protector Diameter, minimum	3.50 mm 0.14 in
Splice Protector Length, maximum	45.00 mm 1.77 in
Splice Protector Length, minimum	35.00 mm 1.38 in
Splice Tray Chip Type	Heat shrink
Splice Tray Construction	R12 (for 1 ribbon 12 strip)
Splice Tray Included, quantity	2
Splices per Tray, note	1 mass splice (12-ribbon) per tray
Splices per Tray, quantity	1
Used UMS Units, quantity	3

Dimensions

Height	12.00 mm 0.47 in
Length	152.00 mm 5.98 in
Weight	0.10 kg 0.22 lb
Width	102.00 mm 4.02 in

Dimension Drawing



Dimension Drawing

Used as an image placeholder

Mechanical Specifications

Material Type	PBT PET
Minimum Bend Radius, standard	30.00 mm 1.18 in

Environmental Specifications

Environmental Space	Indoor Outdoor
Relative Humidity	93%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



* Footnotes

Used UMS Units, quantity The overall used splice tray height is expressed in UMS units. One UMS unit equals 6 mm.