



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 96 E2000/APC, singlemode, right oriented, putty white

## Product Classification

<b>Product Series</b>	NGF
<b>Product Type</b>	Fiber patch/splice block
<b>Regional Availability</b>	EMEA   Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Depth</b>	495.30 mm   19.50 in
<b>Height</b>	558.80 mm   22.00 in
<b>Width</b>	166.88 mm   6.57 in

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Qualification Standards</b>	Telcordia GR-449-CORE
<b>Relative Humidity</b>	Up to 80%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Shelf Movement</b>	Fixed
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Right orientation
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Door Type, front</b>	Compression latch   Hinged
<b>Functionality</b>	Patching   Splicing

<b>Growth Configuration</b>	Fully loaded
<b>Includes</b>	Mounting hardware
<b>Interface Feature, front</b>	APC
<b>Interface, front</b>	E2000
<b>Package Quantity</b>	1
<b>Rack Type</b>	NGF
<b>Total Ports, quantity</b>	96

## Mechanical Specifications

**Cable Exit Location** Rear, bottom side

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

