



Next Generation Frame (NGF) Fiber Termination Block with IFC Cable, singlemode, 96 E2000/APC to Stub tail, left oriented, upward cable exit, putty white, 30 m

Product Classification

Product Series	NGF
Product Type	Fiber patch block, with IFC cable
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Cable Stub Length	30 m 98 ft
Depth	434.34 mm 17.10 in
Height	239.27 mm 9.42 in
Width	153.42 mm 6.04 in

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Qualification Standards	Telcordia GR-449-CORE
Relative Humidity	Up to 80%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Shelf Movement	Fixed
Application	Used in NGF-style frames only
Body Style	Left orientation
Cable Stub Type	IFC, stranded
Color	Putty white
Color, front	Putty white

Door Type, front	Compression latch Hinged
Functionality	Patching
Growth Configuration	Fully loaded
Interface Feature, front	APC
Interface, front	E2000
Interface, rear	Stub tail
Package Quantity	1
Rack Type	NGF
Total Ports, quantity	96

Mechanical Specifications

Cable Exit Location	Upward
----------------------------	--------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

