



TRAC Copper Closure, unpressurized, gel sealed, 22 inch sheath opening, 34 inch long

- Toolless, extendable and re-enterable closure for freebreathing aerial applications
- Consists of three main components: a central body and two end pieces and self support bond system
- Unique convoluted design provides both mechanical and environmental protection
- Recommended for use on polyethylene insulated cable jackets for straight and branch configurations

## Product Classification

<b>Product Type</b>	Gel sealed closure
<b>Product Series</b>	TRAC
<b>Regional Availability</b>	Latin America   North America

## General Specifications

<b>Application</b>	For use with Polyethylene cables
<b>Cable Capacity, maximum</b>	2
<b>Color</b>	Black
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Single Cable Diameter, maximum</b>	48.26 mm   1.90 in
<b>Splice Bundle Diameter, maximum</b>	127.00 mm   5.00 in
<b>Splicing Capacity, maximum</b>	600

## Dimensions

<b>Length</b>	863.60 mm   34.00 in
<b>Sheet Opening, nominal</b>	558.80 mm   22.00 in

## Mechanical Specifications

<b>Cable Sealing Type</b>	Gel filled
<b>Closure Style</b>	In-line
<b>Mount Type</b>	Strand

## Environmental Specifications

<b>Environmental Space</b>	Aerial
----------------------------	--------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

