

# FDH1206-24SE2-30M



HELIAX® FiberFeed® Direct, 6 RRU (6x12). Top: 12 x 10 AWG EMI shielded power cords blunt cut within 6 outdoor tails, 24 single mode fibers within 12 outdoor tails, compatible with ODC interface. Bottom: power conductors blunt cut, fibers within 12 DLC tails, pre-installed grounding wire, 30 m

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	FiberFeed®   HELIAX®
<b>Product Series</b>	FDH
<b>Product Type</b>	Hybrid cable assembly
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	G.657.A2
<b>Total Fibers, quantity</b>	24
<b>Jacket Color</b>	Black

## Dimensions

<b>Cord Length</b>	30.00 m   98.43 ft
<b>Cable Weight</b>	2370.0 kg/km   1590.0 lb/kft
<b>Diameter Over Jacket</b>	36.00 mm   1.42 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Conductors, quantity</b>	12
<b>Construction Type</b>	Direct breakout trunk
<b>Center Conductor Gauge</b>	6 AWG
<b>Interface Body Style, connector A</b>	Straight
<b>Interface Body Style, connector B</b>	Straight
<b>Interface Feature, connector A</b>	Outdoor
<b>Interface Feature, connector B</b>	Standard
<b>Interface, connector A</b>	ODC-LC
<b>Interface, connector B</b>	DLC
<b>Minimum Bend Radius</b>	360.7 mm   14.2 in
<b>Minimum Bend Radius, furcation</b>	30.0 mm   1.2 in
<b>Ordering Note</b>	CommScope® non-standard product

## Optical Performance

**Assembly Insertion Loss, typical** 0.75 dB

**Assembly Insertion Loss, typical note** Insertion loss is measured at 1310 and 1550 nm

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Assembly Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)