


PowerSUM 2061F ETL Verified Category 5e U/UTP Cable, plenum, red jacket, 4 pair count, 3000 ft (914 m) length, reel

Product Classification

Portfolio	SYSTIMAX®
Brand	PowerSUM
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	FEP Polyolefin

Dimensions

Cable Length	914 m 3000 ft
Cable Length Tolerance	±5%

Cable Weight	22.50 lb/kft
Diameter Over Jacket, nominal	5.080 mm 0.200 in
Jacket Thickness	0.635 mm 0.025 in

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	76 %
Operating Frequency, maximum	200 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-3-1 ISO/IEC 11801 Class D
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

Environmental Space	Plenum
Smoke Test Method	CMP
Flame Test Method	CMP
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Red
Product Number	2061F
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
---------------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

