



Carrier Access Point with 4-Band Support for Low Power DCS 1800, IMT 2100 and IMT 2600 MIMO Applications, Copper Fed, Power over CAT Powered, without Fan Kit

## Product Classification

<b>Brand</b>	Era™
<b>Product Type</b>	Access point

## General Specifications

<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Type</b>	Low

## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>License Band</b>	DCS 1800   IMT 2100   IMT 2600
<b>Voltage Range</b>	-60 to -36 Vdc

## Electrical Specifications Rx (Uplink)

<b>Operating Frequency Band</b>	1710 – 1785 MHz (DCS 1800)   1920 – 1980 MHz (IMT 2100)   2500 – 2570 MHz (IMT 2600)
<b>System Gain Range, nominal</b>	+5 dB to +26 dB
<b>System Input ICP-3, out of sub-band</b>	-5 dBm
<b>System Noise Figure</b>	9.0 dB
<b>System Noise Figure Tolerance</b>	±2 dB

## Mechanical Specifications

<b>RF Antenna Port 2, Band Assignment</b>	21/26
---	-------

## Environmental Specifications

<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67
---------------------------------------	----------------------