


BH-Series Single and Double Block Hangers for Fiber, Power, Hybrid and Coaxial Assemblies

Bulletin 7717392 Revision E Page 1 of 1

Description

BH-series Blocks are designed to secure multiple runs of cable in bundled space saving configurations. Blocks can be mounted directly to existing tower members using single, double, triple, or quadruple stack hardware kits recommended at 3ft (0.9m) intervals. For additional details on spacing, you can reference the CommScope Hanger Spacing Guidelines. www.commscope.com/globalassets/digizuite/968475-7719798.pdf

Block Part No.	Compatible Cable Diameter Range	1-Stack Hardware Part No.	2-Stack Hardware Part No.	3-Stack Hardware Part No.	4-Stack Hardware Part No.
BHD-4MM	5-7 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-14	7-9 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-38	10-12 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-58	17.8-20.1 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-12S	13.5-15.5 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-12	15.2-16.3 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-78	27.7-28.2 mm	3/8" 243095-9 M10 243095-11	3/8" 243095-5 M10 243095-7	3/8" 243095-1 M10 243095-3	3/8" 243095-2 M10 243095-4
BHD-114 / BHS-114	39.6-40.6 mm	3/8" 243095-10 M10 243095-12	3/8" 243095-6 M10 243095-8	3/8" 243095-2 M10 243095-37	3/8" 243095-38 M10 243095-37
BHD-158 / BHS-158	49-51.1 mm	3/8" 243095-10 M10 243095-12	3/8" 243095-6 M10 243095-8	3/8" 243095-2 M10 243095-37	3/8" 243095-38 M10 243095-37



CommScope

3642 E US Highway 70, Claremont, NC 28610 USA
(828) 324-2200 (800) 982-1708
www.commscope.com

Technical Support

+1 888 297 6433, Option 3 (Toll Free US and Canada)
+1 828 323 4220, Option 3 (local)
<https://www.commscope.com/wisupport> (open a ticket)

Notice: CommScope disclaims any liability or responsibility for the results of improper or unsafe installation, inspection, maintenance, or removal practices.
Aviso: CommScope no acepta ninguna obligación ni responsabilidad como resultado de prácticas incorrectas o peligrosas de instalación, inspección, mantenimiento o retiro.
Avis: CommScope décline toute responsabilité pour les conséquences de procédures d'installation, d'inspection, d'entretien ou de retrait incorrectes ou dangereuses.
Hinweis: CommScope lehnt jede Haftung oder Verantwortung für Schäden ab, die aufgrund unsachgemäßer Installation, Überprüfung, Wartung oder Demontage auftreten.
Atenção: A CommScope abdica do direito de toda responsabilidade pelos resultados de práticas inadequadas e sem segurança de instalação, inspeção, manutenção ou remoção.
Avvertenza: CommScope declina eventuali responsabilità derivanti dall'esecuzione di procedure di installazione, ispezione, manutenzione e smontaggio improprie o poco sicure.
注意: CommScope 公司申明對於不恰當或不安全的安裝、檢驗、維修或拆卸操作所導致的後果不負責任 何義務和責任