

4



3

2



1

- 1.0 GENERAL NOTES
  - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]
  - 1.2 FOR PATENT INFO: <https://www.cs-pat.com>
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
  - 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING
  - 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
  - 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
  - 5.3 EXTRA HARDWARE MAY BE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	YX1027 05JUN24	XK1001 40197314CMO



PACKAGING VIEW



<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>												
TOLERANCES						SAP MATERIAL MASTER						
1 PLACE .X[X] ± 0.2[6.3]			3 PLACE .XXX[X] ± 0.060[1.5]			<b>MC-PK-238-238</b>						
2 PLACE .XX[X] ± 0.12[3.0]			ANGLES ± 2°									
FINISH						MATERIAL						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	NAME		DATE		<b>PIPE MNT, SADDLE, CO, 2-3/8" X 96" PIPE</b>							
	CE	YX1027	05JUN24									
	RW	YX1027	06/07/2024									
	AD	XK1001	06/07/2024									
	RE	YMENG	06/12/2024									
ECN 40197314CMO						SCALE <b>1:10</b>		DOCUMENT NO. <b>MC-PK-238-238</b>				
SIZE		Auth Group		INSL		MODEL			DRAWING			SHEET 1 OF 1
<b>C</b>		[Symbol]		[Symbol]		VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	
						00	RE	A	00	RE	A	

DENSITY		lbs/in <sup>3</sup>
MASS	72.41	lbs
VOLUME	255.12	in <sup>3</sup>
SURFACE AREA	3166.49	in <sup>2</sup>
HEIGHT	96"	
LENGTH	7.50"	
WIDTH	8.25"	

4

3

2

1