

1H5935-000 | FIBRBOX-C-12-1-CS



FIBRBOX Fiber Optic pedestal, wall, or pole mount splice enclosure, Buffer tube storage up to 96 fiber cable, 96 single splices or 288 mass fusion, with ground block, and gasket sealed door

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Single-ended, rectangular fiber closure

General Specifications

Functionality	Splicing
Access	Front
Cable Entry Location	Bottom
Enclosure Color	Almond
Front Cover Type	Snap-on cover
Mounting	Pedestal Pole Wall
Port, quantity	24
Splice Tray Construction	SC (Single circuit)
Splice Trays	Included
Splice Trays Included, quantity	1
Splicing Capacity, maximum	48
Splicing Type	Heat shrink, mass fusion Heat shrink, single fiber fusion
Splicing Type, Supported	Mass fusion Single fusion

Dimensions

Height	462.84 mm 18.222 in
Width	203.2 mm 8 in
Depth	106.68 mm 4.2 in

Material Specifications

Material Type	Aluminum
----------------------	----------

1H5935-000 | FIBRBOX-C-12-1-CS

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor/Outdoor

Qualification Standards IEC 60529, IP54 | IEC 61753-1, category G

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

