


760256244 | C-096-LN-5K-M12BK/15D/B2



Fiber indoor/outdoor cable, Low Smoke Zero Halogen, 96 fiber Microsheath, Multi mode OM4 , Gel-free, Meters jacket marking, Black jacket color, B2ca flame rating

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LN


General Specifications

Cable Type	Stranded microsheath tube
Subunit Type	Gel-free
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE 760256143 96 x G652D 9/125 EN50575 CLASS B ULSZH [Serial number] [metre mark]
Fibers per Subunit, quantity	12
Total Fiber Count	96

Dimensions

Buffer Tube/Subunit Diameter	1.5 mm 0.059 in
Diameter Over Jacket	8.7 mm 0.343 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, unloaded	110 mm 4.331 in
Tensile Load, long term, maximum	260 N 58.45 lbf
Tensile Load, short term, maximum	850 N 191.088 lbf
Cable Crush Resistance, maximum	10 N/mm 57.101 lb/in
Compression Test Method	IEC 60794-1-21 E3
Impact	2 N-m 17.701 in lb
Impact Test Method	IEC 60794-1-21 E4
Strain Test Method	IEC 60794-1-21 E1

Optical Specifications

Fiber Type	OM4
-------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.60 dB/km @ 1,300 nm 2.20 dB/km @ 850 nm
-----------------------------	---

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
EN50575 CPR Cable EuroClass Fire Performance	B2ca
EN50575 CPR Cable EuroClass Smoke Rating	s1a

760256244 | C-096-LN-5K-M12BK/15D/B2

EN50575 CPR Cable EuroClass Droplets Rating	d0
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Universal Low Smoke Zero Halogen (ULSZH)
Water Penetration Test Method	IEC 60794-1 F4

Environmental Test Specifications

Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-22 F1

Packaging and Weights

Cable weight	83.6 kg/km 56.177 lb/kft
---------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant



Included Products

NW-OM4B-LT – 50µm OM4 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable