MPTA06BDBBNN-500M



HELIAX® Power cable, with aluminum shield with quantity $6 \ x \ 10 \mbox{mm}^2$, flame resistant CPR Class Dca. rated, 500 meters

• Available with different colors on demand

Product Classification

Regional Availability	Europe
Product Type	Power cable
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product
Warranty	For more information, please consult our Product Warranty guidelines

General Specifications

Application	Remote radio head	
Cable Type	Power	
Conductor Type, singles	Stranded	
Conductors, quantity	6	
Jacket Color	Black	
Jacket Color, singles	Blue Brown	
Outer Shield (Tape) Material	AI/PET tape	
Dimensions		
Cable Length	500.024 m 1,640.5 ft	
Diameter Over Jacket, maximum	17.983 mm 0.708 in	
Conductor Gauge	10 mm² class 5	
Electrical Specifications		

600 V


Safety Voltage Rating

Ordering Tree

Page 1 of 3



MPTA06BDBBNN-500M



Notes

this size is not available for 6, 8, or 12 core cable options.

** this size is not available for 8 and 12 core cable options.

Material Specifications

Ground Wire Material	Annealed aluminum wires	
Insulation Material, singles	Flame retardant PE	
Jacket Material	Flame retardant PE Low Smoke Zero Halogen (LSZH)	
Outer Shield (Braid) Coverage	100 %	
Outer Shield (Tape) Material	AI/PET tape	

Environmental Specifications

Installation temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-40 °C to +90 °C (-40 °F to +194 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Environmental Space	Indoor/Outdoor
Jacket UV Resistance	UV stabilized

Packaging and Weights

Cable	weight
-------	--------

170.008 kg/km | 114.24 lb/kft

* Footnotes

Page 2 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

MPTA06BDBBNN-500M

Warranty

For more information, please consult our Product Warranty guidelines

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025