

XP-RM1.5U-6C



XPND 1.5Ru empty panel, accepts 6 XPND modular cassettes, providing up to 72 SC ports or 144 LC ports

- Components can be installed and removed from front or rear of panel
- Supports 8f, 12f, 16f and 24f applications while maintaining full panel density
- Cable mounting system allows for multiple trunk cables to be securely attached in the rear of panel

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber patch panel
Product Brand	XPND®

General Specifications

Color	White
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1.5
Shelf Movement	Fixed
Total Ports, quantity	0

Dimensions

Height	66.67 mm 2.625 in
Width	431.8 mm 17 in
Depth	304.8 mm 12 in

Material Specifications

Material Type	Aluminum Steel
---------------	------------------

Environmental Specifications

Safety Standard	c-UL-us
-----------------	---------

Packaging and Weights

Packaging quantity	1
--------------------	---

XP-RM1.5U-6C

Weight, net 5.375 kg | 11.85 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

