

Fiber indoor cable, All-Dielectric, LSZH/Riser-Rated, Gel-Free, Central Tube 200µm Rollable Ribbon, 288 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Cca flame rating

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Fiber indoor cable

### Product Series

N-CN

## General Specifications

### Cable Type

Ribbon central tube

### Construction Type

Non-armored

### Subunit Type

Gel-free

### Fibers per Ribbon, quantity

16

### Jacket Color

Yellow

### Jacket Marking

Feet

### Total Fiber Count

288

## Dimensions


### Buffer Tube/Subunit Diameter

6.5 mm | 0.256 in

### Diameter Over Jacket

10.9 mm | 0.429 in

## Representative Image



\*Picture shows cable design for 432F or higher where ribbons are bundled in groups of 144F per bundle.  
\*144F & 288F count designs use water blocking threads rather than a water blocking tape inside the buffer tube.

## Mechanical Specifications

|   |                                       |
|---|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>        | 109 mm   4.291 in                     |
| <b>Minimum Bend Radius, storage coils</b> | 218 mm   8.583 in                     |
| <b>Minimum Bend Radius, unloaded</b>      | 55 mm   2.165 in                      |
| <b>Tensile Load, long term, maximum</b>   | 800 N   179.847 lbf                   |
| <b>Tensile Load, short term, maximum</b>  | 2700 N   606.984 lbf                  |
| <b>Compression</b>                        | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>            | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                               | 25 cycles                             |
| <b>Flex Test Method</b>                   | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                             | 2.94 N-m   26.021 in lb               |
| <b>Impact Test Method</b>                 | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                             | See long and short term tensile loads |
| <b>Strain Test Method</b>                 | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                              | 10 cycles                             |
| <b>Twist Test Method</b>                  | FOTP-85   IEC 60794-1 E7              |

## Optical Specifications

|                   |                           |
|-------------------|---------------------------|
| <b>Fiber Type</b> | G.657.A2/B2   G.657.A2/B2 |
|-------------------|---------------------------|

## Environmental Specifications

# 760259253 | N-288-CN-RR-F16YL/8G1/99P/200 /C

|   |   |
|---|---|
| <b>Installation temperature</b>                     | -20 °C to +60 °C (-4 °F to +140 °F)                                     |
| <b>Operating Temperature</b>                        | -40 °C to +70 °C (-40 °F to +158 °F)                                    |
| <b>Storage Temperature</b>                          | -40 °C to +70 °C (-40 °F to +158 °F)                                    |
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-104-696   EN 187105   Telcordia GR-409                      |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Cca   |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1a   |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d1  |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a1  |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)   Riser                                   |
| <b>Flame Test Listing</b>                           | NEC OFNR-ST1 (ETL) and c(ETL)   |
| <b>Flame Test Method</b>                            | CSA FT4   IEC 60332-1-2   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685 |

## Environmental Test Specifications

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| <b>Low High Bend</b>                 | -20 °C to +60 °C (-4 °F to +140 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11           |
| <b>Temperature Cycle</b>             | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1             |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 95 kg/km   63.837 lb/kft |
|---------------------|--------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>   |
|---------------|---|
| CHINA-ROHS    | Below maximum concentration value   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant   |
| UK-ROHS       | Compliant   |



## Included Products

|                |   |   |
|----------------|---|---|
| CS-8G-200UM-LT | - | 200 Micron Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2) |
|----------------|---|---|

## \* Footnotes

760259253 | N-288-CN-RR-F16YL/8G1/99P/200  
/C

---

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable