



FACT® Fiber Optic Splice Chassis, gray, 3E high, loaded with 36 trays for holding up to 12 ANT type splices per tray

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice chassis
Product Brand	FACT®
Product Series	FACT

General Specifications

Functionality	Splicing
Application	Compatible with FIST-GR3-style frames
Body Style	Symmetrical
Color	Gray
Growth Configuration	Fully loaded
Interface, front	Unloaded
Rack Type	FACT FIST-GR3
Rack Units	2.1
Shelf Movement	Sliding
Splicing Capacity, maximum	432
Splicing Type	ANT
Total Ports, quantity	0
Transmission Standards	ETSI EN 300 019-1-3 IEC 61300-3-30

760258493 | FACT-3ESPLA12HD


Dimensions

Height	92.85 mm 3.656 in
Width	524 mm 20.63 in
Depth	283 mm 11.142 in

Splicing Configuration

NUMBER OF TRAYS PER FACT-CHASSIS				
	A04	S04	A12	S12
1E	12	12	8	6
2E	24	24	16	12
3E	36	36	24	18
4E	48	48	32	24

Ordering Tree



Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

Packaging and Weights

Included	Mounting hardware for FACT frame
Packaging quantity	1