

# SURGE-ARRESTORS

---

Base Product



Arrestor Plus® Dual Band Quarterwave and Gas Tube Surge Arrestors

## Product Classification

<b>Product Type</b>	Surge arrestor
<b>Product Brand</b>	Arrestor Plus®

## Electrical Specifications

<b>Connector Impedance</b>	50 ohm
<b>Lightning Surge Current Waveform</b>	8/20 waveform

## Mechanical Specifications

<b>Interface Durability Method</b>	IEC 61169-16:9.5
------------------------------------	------------------

## Environmental Specifications

<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Immersion Depth</b>	1 m
<b>Immersion Test Mating</b>	Mated
<b>Immersion Test Method</b>	IEC 60529:2001, IP68