



Heat treated LDF1RK-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated fire retardant jacket

Product Classification

Product Type	Coaxial wireless cable
Product Brand	HELIAX®
Product Series	LDF1-50

General Specifications

Flexibility	Standard
Jacket Color	Black
Performance Note	Attenuation values typical, guaranteed within 5%

Dimensions

Diameter Over Dielectric	6.858 mm 0.27 in
Diameter Over Jacket	9.017 mm 0.355 in
Inner Conductor OD	2.54 mm 0.1 in
Outer Conductor OD	7.874 mm 0.31 in
Nominal Size	1/4 in

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm
Capacitance	77 pF/m 23.47 pF/ft
dc Resistance, Inner Conductor	5.151 ohms/km 1.57 ohms/kft
dc Resistance, Outer Conductor	4.003 ohms/km 1.22 ohms/kft
dc Test Voltage	2200 V
Inductance	0.059 µH/m 0.018 µH/ft
Insulation Resistance	100000 MOhms-km
Jacket Spark Test Voltage (rms)	5000 V
Operating Frequency Band	1 – 15800 MHz
Peak Power	12.1 kW

Velocity

86 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.394	0.12	12.1
1.5	0.483	0.147	12.1
2.0	0.558	0.17	12.1
10.0	1.254	0.382	5.83
20.0	1.781	0.543	4.11
30.0	2.188	0.667	3.34
50.0	2.838	0.865	2.58
85.0	3.724	1.135	1.96
88.0	3.791	1.156	1.93
100.0	4.049	1.234	1.81
108.0	4.213	1.284	1.74
150.0	4.993	1.522	1.47
174.0	5.392	1.644	1.36
200.0	5.798	1.767	1.26
204.0	5.858	1.785	1.25
300.0	7.168	2.185	1.02
400.0	8.342	2.543	0.88
450.0	8.88	2.706	0.82
460.0	8.984	2.738	0.81
500.0	9.391	2.862	0.78
512.0	9.511	2.899	0.77
600.0	10.351	3.155	0.71
700.0	11.244	3.427	0.65
800.0	12.084	3.683	0.61
824.0	12.278	3.742	0.6
894.0	12.833	3.911	0.57
960.0	13.339	4.066	0.55
1000.0	13.639	4.157	0.54
1218.0	15.192	4.63	0.48
1250.0	15.41	4.697	0.47
1500.0	17.04	5.194	0.43

35422-57

1700.0	18.266	5.567	0.4
1794.0	18.823	5.737	0.39
1800.0	18.858	5.748	0.39
2000.0	20.003	6.097	0.37
2100.0	20.559	6.266	0.36
2200.0	21.104	6.432	0.35
2300.0	21.64	6.596	0.34
2500.0	22.686	6.914	0.32
2700.0	23.701	7.224	0.31
3000.0	25.171	7.672	0.29
3400.0	27.048	8.244	0.27
3600.0	27.956	8.521	0.26
3700.0	28.403	8.657	0.26
3800.0	28.846	8.792	0.25
3900.0	29.284	8.925	0.25
4000.0	29.719	9.058	0.25
4100.0	30.149	9.189	0.24
4200.0	30.576	9.319	0.24
4300.0	30.999	9.448	0.24
4400.0	31.419	9.576	0.23
4500.0	31.835	9.703	0.23
4600.0	32.249	9.829	0.23
4700.0	32.659	9.954	0.22
4800.0	33.066	10.078	0.22
4900.0	33.47	10.201	0.22
5000.0	33.871	10.323	0.22
6000.0	37.742	11.503	0.19
8000.0	44.888	13.681	0.16
8800.0	47.579	14.501	0.15
10000.0	51.475	15.689	0.14
12000.0	57.664	17.575	0.13
14000.0	63.552	19.37	0.12
15800.0	68.646	20.922	0.11

Material Specifications

Dielectric Material

Foam PE

35422-57

Jacket Material	Non-halogenated, fire retardant polyolefin
Inner Conductor Material	Copper-clad aluminum wire
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	76.2 mm 3 in
Minimum Bend Radius, single Bend	38.1 mm 1.5 in
Number of Bends, minimum	15
Number of Bends, typical	30
Tensile Strength	91 kg 200.62 lb
Bending Moment	1.4 N-m 12.391 in lb
Flat Plate Crush Strength	1.4 kg/mm 78.396 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C
Fire Retardancy Test Method	NFPA 130-2010 UL 1666/CATVR
Smoke Index Test Method	IEC 61034
Toxicity Index Test Method	IEC 60754-1 IEC 60754-2

Packaging and Weights

Cable weight	0.09 kg/m 0.06 lb/ft
---------------------	------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system