EW132, HELIAX® Standard Elliptical Waveguide, 14.0–14.5 GHz, black PE jacket



OBSOLETE This product was discontinued on: January 2, 2024

Product Classification

Product Type		Standard elliptical waveguide
Product Brand		HELIAX®
Product Series		Standard
General Specifications		
Jacket Color		Black
Performance Note		Values typical, unless otherwise stated
Dimensions		
Diameter Over Jacket (E Plane)		24.4 mm 0.961 in
Diameter Over Jacket (H Plane)		15.5 mm 0.61 in
Cable Volume		167 L/km 1.798 ft³/kft
Electrical Specifications		
eTE11 Mode Cutoff		9.22 GHz
Group Delay at Frequency		131 ns/100 ft @ 14.700 GHz 428 ns/100 m @ 14.700 GHz
Operating Frequency Band		14.0 – 14.5 GHz
VSWR/Return Loss		
Frequency Band	VSWR	Return Loss (dB)
14.0–14.5 GHz	1.15	23.13

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 16, 2024



EW132-140

Attenuation

Frequency (GHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
14.0	16.343	4.982	0.826	75.3
14.2	16.174	4.93	0.835	76.1
14.4	16.018	4.882	0.843	76.8
Material Specifications				
Conductor Material	C	Corrugated copper		
Jacket Material	Ρ	ΡE		
Mechanical Specifications	5			
Minimum Bend Radius, Multiple Bends (E Plane)		30 mm 5.118 in		
Minimum Bend Radius, Multiple Bends	(H Plane) 3	60 mm 14.173 in		
Minimum Bend Radius, Single Bend (E	Plane) 1	30 mm 5.118 in		
Minimum Bend Radius, Single Bend (H	Plane) 3	60 mm 14.173 in		
Maximum Twist	6	.562 °/m 2 °/ft		
Environmental Specificati	ions			
Installation temperature		40 °C to +60 °C (-40 °F to +14	40 °F)	
Operating Temperature		55 °C to +85 °C (-67 °F to +18	,	
Storage Temperature	-7	70 °C to +85 °C (-94 °F to +18	35 °F)	
Attenuation, Ambient Temperature	7	75°F 23.889°C		
Average Power, Ambient Temperature	1	04 °F 40 °C		
Average Power, Temperature Rise	4	2°C 107.6°F		
Packaging and Weights				
Cable weight	0	.33 kg/m 0.222 lb/ft		
Regulatory Compliance/C	Certifications			

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 16, 2024





UK-ROHS

Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 16, 2024

