

# EW220



EW220, HELIAX® Standard Elliptical Waveguide, 21.2–23.6 GHz, black PE jacket

## Product Classification

<b>Product Type</b>	Standard elliptical waveguide
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	Standard

## General Specifications

<b>Jacket Color</b>	Black
<b>Performance Note</b>	Values typical, unless otherwise stated

## Dimensions

<b>Diameter Over Jacket (E Plane)</b>	17.8 mm   0.701 in
<b>Diameter Over Jacket (H Plane)</b>	11.2 mm   0.441 in
<b>Cable Volume</b>	74 L/km   0.797 ft³/kft

## Electrical Specifications

<b>eTE11 Mode Cutoff</b>	13.338 GHz
<b>Group Delay at Frequency</b>	127 ns/100 ft @ 22.400 GHz   415 ns/100 m @ 22.400 GHz
<b>Operating Frequency Band</b>	21.2 – 23.6 GHz

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
21.2–23.6 GHz	1.15	23.13

## Attenuation

Frequency (GHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
21.2	28.042	8.547	0.398	77.7
21.6	27.799	8.473	0.401	78.7
22.0	27.577	8.406	0.404	79.5
22.4	27.376	8.344	0.407	80.3

# EW220

---

<b>22.8</b>	27.192	8.288	0.41	81.1
<b>23.2</b>	27.024	8.237	0.413	81.8
<b>23.6</b>	26.87	8.19	0.415	82.5

## Material Specifications

<b>Conductor Material</b>	Corrugated copper
<b>Jacket Material</b>	PE

## Mechanical Specifications

<b>Minimum Bend Radius, Multiple Bends (E Plane)</b>	120 mm   4.724 in
<b>Minimum Bend Radius, Multiple Bends (H Plane)</b>	230 mm   9.055 in
<b>Minimum Bend Radius, Single Bend (E Plane)</b>	120 mm   4.724 in
<b>Minimum Bend Radius, Single Bend (H Plane)</b>	230 mm   9.055 in
<b>Maximum Twist</b>	6.562 °/m   2 °/ft

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	75 °F   23.889 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Temperature Rise</b>	42 °C   107.6 °F

## Packaging and Weights

<b>Cable weight</b>	0.18 kg/m   0.121 lb/ft
---------------------	-------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



