

# N-002-DS-6F-FSU

Fiber indoor cable, OptiSPEED® Low Smoke Zero Halogen Riser Distribution, 2 fiber single-unit, Singlemode G.652.D and G.657.A1, Feet jacket marking, Dca flame rating

## Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| Portfolio             | CommScope®  |
| Product Type          | Fiber indoor cable  |
| Product Series        | N-DS  |

## General Specifications

|                   |              |
|-------------------|--------------|
| Cable Type        | Distribution |
| Construction Type | Non-armored  |
| Subunit Type      | Gel-free     |
| Jacket Marking    | Feet         |
| Total Fiber Count | 2            |

## Dimensions

|                      |                    |
|----------------------|--------------------|
| Diameter Over Jacket | 3.71 mm   0.146 in |
|----------------------|--------------------|

## Representative Image



## Mechanical Specifications

# N-002-DS-6F-FSU

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 56 mm   2.205 in                      |
| Minimum Bend Radius, unloaded     | 37 mm   1.457 in                      |
| Tensile Load, long term, maximum  | 200 N   44.962 lbf                    |
| Tensile Load, short term, maximum | 667 N   149.948 lbf                   |
| Compression                       | 10 N/mm   57.101 lb/in                |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 100 cycles                            |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 2.94 N-m   26.021 in lb               |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 500 m   1,640.42 ft                   |

## Optical Specifications

|            |                                   |
|------------|-----------------------------------|
| Fiber Type | OM1, OptiSPEED®   OM1, OptiSPEED® |
|------------|-----------------------------------|

## Environmental Specifications

|  |   |
|--|---|
| Installation temperature                     | -10 °C to +60 °C (+14 °F to +140 °F)                        |
| Operating Temperature                        | -20 °C to +70 °C (-4 °F to +158 °F)                         |
| Storage Temperature                          | -40 °C to +70 °C (-40 °F to +158 °F)                        |
| Cable Qualification Standards                | ANSI/ICEA S-83-596   Telcordia GR-409                       |
| EN50575 CPR Cable EuroClass Fire Performance | Dca   |
| EN50575 CPR Cable EuroClass Smoke Rating     | s1a   |
| EN50575 CPR Cable EuroClass Droplets Rating  | d0  |
| EN50575 CPR Cable EuroClass Acidity Rating   | a2  |
| Environmental Space                          | Low Smoke Zero Halogen (LSZH)   Riser                       |
| Flame Test Listing                           | NEC OFNR-ST1 (ETL) and c(ETL)                               |
| Flame Test Method                            | IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685 |

## Environmental Test Specifications

# N-002-DS-6F-FSU

|                               |                                      |
|-------------------------------|--------------------------------------|
| Heat Age                      | -20 °C to +85 °C (-4 °F to +185 °F)  |
| Heat Age Test Method          | IEC 60794-1 F9                       |
| Low High Bend                 | -10 °C to +60 °C (+14 °F to +140 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11            |
| Temperature Cycle             | -20 °C to +70 °C (-4 °F to +158 °F)  |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1              |

## Packaging and Weights

|              |                         |
|--------------|-------------------------|
| Cable weight | 12 kg/km   8.064 lb/kft |
|--------------|-------------------------|

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available                 |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



## Included Products

- CS-6F-TB – OptiSPEED® OM1 Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

OptiSPEED®

Product Classification

|              |               |
|--------------|---------------|
| Portfolio    | CommScope®    |
| Product Type | Optical fiber |

General Specifications

|   |                        |
|---|------------------------|
| Cladding Diameter                             | 125 µm                 |
| Cladding Diameter Tolerance                   | ±1.0 µm                |
| Cladding Non-Circularity, maximum             | 1 %                    |
| Coating Diameter (Colored)                    | 254 µm                 |
| Coating Diameter (Uncolored)                  | 245 µm                 |
| Coating Diameter Tolerance (Colored)          | ±7 µm                  |
| Coating Diameter Tolerance (Uncolored)        | ±10 µm                 |
| Coating/Cladding Concentricity Error, maximum | 12 µm                  |
| Core Diameter                                 | 62.5 µm                |
| Core Diameter Tolerance                       | ±2.5 µm                |
| Core/Clad Offset, maximum                     | 1 µm                   |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa) |
| Tight Buffer Diameter                         | 900 µm                 |
| Tight Buffer Diameter Tolerance               | ±40 µm                 |

Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| Macrobending, 75 mm Ø mandrel, 100 turns | 0.50 dB @ 1,300 nm   0.50 dB @ 850 nm |
| Coating Strip Force, maximum             | 8.9 N   2.001 lbf                     |
| Coating Strip Force, minimum             | 1.3 N   0.292 lbf                     |
| Dynamic Fatigue Parameter, minimum       | 18                                    |

Optical Specifications

|                    |       |
|--------------------|-------|
| Numerical Aperture | 0.275 |
|--------------------|-------|

# CS-6F-TB

|                                     |                     |
|-------------------------------------|---------------------|
| Numerical Aperture Tolerance        | ±0.015              |
| Point Defects, maximum              | 0.15 dB             |
| Zero Dispersion Slope, maximum      | 0.097 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1365 nm             |
| Zero Dispersion Wavelength, minimum | 1320 nm             |

## Optical Specifications, Wavelength Specific

|                          |   |
|--------------------------|---|
| 1 Gbps Ethernet Distance | 300 m @ 850 nm   550 m @ 1,300 nm           |
| Attenuation, maximum     | 1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm |
| Backscatter Coefficient  | -68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm     |
| Bandwidth, OFL, minimum  | 220 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm |
| Index of Refraction      | 1.491 @ 1,300 nm   1.496 @ 850 nm           |
| Standards Compliance     | TIA-492AAAA (OM1)                           |

## Environmental Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| Heat Aging, maximum                   | 0.20 dB/km @ 85 °C |
| Temperature Dependence, maximum       | 0.1 dB/km          |
| Temperature Humidity Cycling, maximum | 0.2 dB/km          |
| Water Immersion, maximum              | 0.20 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

|                                       |   |
|---------------------------------------|---|
| Temperature Dependence, maximum       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)                                   |
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |