

3-599148-7

Fiber Optic Cable, 12-fiber, OM2 BIF, 3000 m, orange

OBSOLETE

This product was discontinued on: June 13, 2018

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-DS

General Specifications

Cable Type	Tight buffer
Jacket Color	Orange
Jacket Marking	Meters
Fibers per Subunit, quantity	12
Total Fiber Count	12

Dimensions

Cable Length	3000 m 9,842.52 ft
Diameter Over Jacket	7.5 mm 0.295 in

Mechanical Specifications

Minimum Bend Radius, loaded	115 mm 4.528 in
Minimum Bend Radius, unloaded	75 mm 2.953 in
Tensile Load, long term, maximum	600 N 134.885 lbf
Tensile Load, short term, maximum	1000 N 224.809 lbf

Optical Specifications

Fiber Type	OM2, bend insensitive
------------	-----------------------

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.70 dB/km @ 1,300 nm
----------------------	-----------------------

Standards Compliance		IEC 60794-1 TIA-492AAAB (OM2)
Environmental Specifications		
Installation temperature		-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature		-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature		-20 °C to +70 °C (-4 °F to +158 °F)
EN50575 CPR Cable EuroClass Fire Performance		Dca
EN50575 CPR Cable EuroClass Smoke Rating		s2
EN50575 CPR Cable EuroClass Droplets Rating		d1
EN50575 CPR Cable EuroClass Acidity Rating		a1
Environmental Space		Universal Low Smoke Zero Halogen (ULSZH)

Packaging and Weights

Cable weight	56 kg/km 37.63 lb/kft
--------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable