

# NGF-MPQROC416

---



Next Generation Frame (NGF) Fiber Termination Block, 192 LC/UPC, multimode, right oriented, putty white, MPO at rear end

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber patch block
<b>Product Series</b>	NGF

## General Specifications

<b>Functionality</b>	Patching
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Right orientation
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Door Type, front</b>	Compression latch   Hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Rack Type</b>	NGF
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	192

## Dimensions

<b>Height</b>	239.268 mm   9.42 in
<b>Width</b>	153.416 mm   6.04 in
<b>Depth</b>	434.34 mm   17.1 in

## Material Specifications

# NGF-MPQROC416

---

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Multimode

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 80%, non-condensing

**Qualification Standards** Telcordia GR-449-CORE

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

